

Product designation				Signal beacons
Product type designation				Ø62mm/2.44" 8LB6S
General characteristics				
Diameter			mm - inch	62mm / 2.44"
Supply voltage (AC)			V	24
Supply voltage (DC)			V	24
Colour				Blue
Material				Polycarbonate
IEC degree of protection				IP54
Sound module consumption (AC)			mA	150
Sound module consumption (DC)			mA	150
Sound intensity			dB	80dB/1m
Mechanical features				
Tightening torque for terminals max			Nm	0.5
Terminals screw				Screw clamp terminals
Conductor section	AWG/Kcmil			
		max		16
	IEC			
		max	mm ²	1.5
Weight			g	60
Ambient conditions				
Temperature	Operating temperature			
		min	°C	-20
		max	°C	+50
Dimensions				
Wiring diagrams				
Certifications and compliance				
Compliance	IEC/EN 60947-1			
	IEC/EN 60947-5-1			
Certificates	EAC			
ETIM classification				
ETIM 8.0				EC000232 - Optical module for signal tower