

Product designation				Signal tower
Product type designation				Ø45mm/1.7"
General characteristics				
Diameter			mm - inch	45mm / 1.77"
Supply voltage (DC)			V	24±10%
Colour				Green, orange, red
Material				Polycarbonate
IEC degree of protection				IP54
Light consumption per module (DC)			mA	37
Mechanical features				
Tightening torque for terminals max			Nm	0.5
Terminals screw				Screw clamp terminals
Conductor section				
	AWG/Kcmil			
		max	16	
	IEC			
		max	mm ²	1.5
Weight			g	240
Ambient conditions				
Temperature	Operating temperature			
		min	°C	-20
		max	°C	+50
Dimensions				
Wiring diagrams				
Certifications and compliance				
Compliance	CSA C22.2 n° 14			
	IEC/EN 60947-1			
	IEC/EN 60947-5-1			
	UL508			
Certificates	cULus			
	EAC			
ETIM classification				
ETIM 8.0				EC001042 - Signal tower complete