

Product designation				Signal tower Ø45mm/1.7"
Product type designation				8TL4
General characteristics				
Diameter			mm - inch	45mm / 1.77"
Supply voltage (DC)			V	24±10%
Colour				Green, blue, orange, red
Material				Polycarbonate
IEC degree of protection				IP54
Light consumption per module (DC)			mA	37
Sound module consumption (DC)			mA	15
Sound intensity			dB	80dB/1m pulsed or continuous sound
Mechanical features				
Tightening torque for terminals max			Nm	0.5
Terminals screw				Screw clamp terminals
Conductor section	AWG/Kcmil			
		max		16
	IEC			
		max	mm ²	1.5
Weight			g	400
Ambient conditions				
Temperature	Operating temperature			
		min	°C	-20
		max	°C	+50
Dimensions				
Wiring diagrams				
Certifications and compliance				
Compliance	CSA C22.2 n° 14			
	IEC/EN 60947-1			
	IEC/EN 60947-5-1			
	UL508			
Certificates	cULus			
	EAC			
ETIM classification				
ETIM 8.0				EC001042 - Signal tower complete