

Product designation	Signal tower Ø70mm/2.75"		
Product type designation	8LT7S - Sound modules		
General characteristics			
Diameter	mm - inch	70mm / 2.75"	
Supply voltage (AC)	V	24	
Supply voltage (DC)	V	24	
Colour	Grey		
Material	Polycarbonate		
IEC degree of protection	IP65		
Sound module consumption (AC)	mA	200	
Sound module consumption (DC)	mA	200	
Sound intensity	dB	78dB/1m pulsed or 75dB/1m continuous sound	
Mechanical features			
Tightening torque for terminals max	Nm	0.5	
Terminals screw	Screw clamp terminals		
Conductor section			
	AWG/Kcmil	max	16
	IEC	max	mm ² 1.5
Weight		g	240
Ambient conditions			
Temperature	Operating temperature		
	min	°C	-20
	max	°C	+50
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance	CSA C22.2 n°14		
	IEC/EN 60947-1		
	IEC/EN 60947-5-1		
	UL508		
Certificates	cULus		
	EAC		
ETIM classification			
ETIM 8.0	EC001261 - Acoustic module for signal tower		