

Product designation	Signal tower		
	Ø70mm/2.75"		
Product type designation	8LT7S - Sound modules		
<b>General characteristics</b>			
Diameter	mm - inch	70mm / 2.75"	
Supply voltage (AC)	V	110...120	
Colour	Grey		
Material	Polycarbonate		
IEC degree of protection	IP65		
Sound module consumption (AC)	mA	40	
Sound intensity	dB	78dB/1m pulsed or 75dB/1m continuous sound	
<b>Mechanical features</b>			
Weight	g	240	
<b>Ambient conditions</b>			
Temperature	Operating temperature		
	min	°C	-20
	max	°C	+50
<b>Dimensions</b>			
<b>Wiring diagrams</b>			
<b>Certifications and compliance</b>			
Compliance	CSA C22.2 n°14		
	IEC/EN 60947-1		
	IEC/EN 60947-5-1		
	UL508		
Certificates	cULus		
	EAC		
<b>ETIM classification</b>			
ETIM 8.0	EC001261 - Acoustic module for signal tower		