

Product designation				Signal tower Ø70mm/2.75"
Product type designation				8LT7S - Sound modules
General characteristics				
Diameter			mm - inch	70mm / 2.75"
Supply voltage (AC)			V	230...240
Colour				Grey
Material				Polycarbonate
IEC degree of protection				IP65
Sound module consumption (AC)			mA	30
Sound intensity			dB	78dB/1m pulsed or 75dB/1m continuous sound
Mechanical features				
Tightening torque for terminals max			Nm	0.5
Terminals screw				Screw clamp terminals
Conductor section	AWG/Kcmil			
		max		16
	IEC			
		max	mm ²	1.5
Weight			g	240
Ambient conditions				
Temperature	Operating temperature			
		min	°C	-20
		max	°C	+50
Dimensions				
Wiring diagrams				
Certifications and compliance				
Compliance	CSA C22.2 n°14			
	IEC/EN 60947-1			
	IEC/EN 60947-5-1			
	UL508			
Certificates	cULus			
	EAC			
ETIM classification				
ETIM 8.0				EC001261 - Acoustic module for signal tower