

Product designation	Pushbutton actuators, spring return, with symbol		
Product type designation	LPCB11		
General characteristics			
Colour	White		
Type of positions	Flush		
Material	Polyamide		
IEC degree of protection	IP66, IP67 and IP69K		
Mechanical features			
Operating force	kg-lb	<0.5Kg / 1.1lb	
Mechanical life	cycles	5000000	
Fixing	Without mounting adapter		
Mounting adapter	LPXAU120		
Weight	g	25	
UL technical data			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions			
Temperature			
Operating temperature		min	°C -25
		max	°C +70
Storage temperature		min	°C -40
		max	°C +85
Dimensions			
Certifications and compliance			
Compliance			
CSA C22.2 n° 14			
IEC/EN/BS 60947-1			
IEC/EN/BS 60947-5-1			
UL508			
Certificates			
CCC			
cULus			
EAC			
RINA			
ETIM classification			
ETIM 8.0	EC000221 - Front element for push button		