

| | | | |
|---|--|---------------------|--------|
| Product designation | Pushbutton actuator, spring return | | |
| Product type designation | LPCB30 | | |
| General characteristics | | | |
| Colour | White | | |
| Type of positions | Shrouded | | |
| Material | Polyamide | | |
| IEC degree of protection | IP66, IP67 and IP69K | | |
| Mechanical features | | | |
| Operating force | kg-lb | <0.5Kg / 1.1lb | |
| Mechanical life - spring return actuators | cycles | 5000000 | |
| Mechanical life - Push-Push actuators | cycles | 500000 | |
| Fixing | Without mounting adapter | | |
| Mounting adapter | LPXAU120 | | |
| Weight | g | 27 | |
| UL technical data | | | |
| UL degree of protection | Type1, 2, 3R, 4, 4X, 12, 12K | | |
| Ambient conditions | | | |
| Temperature | | | |
| Operating temperature | | min | °C -25 |
| | | max | °C +70 |
| Storage temperature | | min | °C -40 |
| | | max | °C +85 |
| Dimensions | | | |
| Certifications and compliance | | | |
| Compliance | | | |
| | | CSA C22.2 n° 14 | |
| | | IEC/EN/BS 60947-1 | |
| | | IEC/EN/BS 60947-5-1 | |
| | | UL508 | |
| Certificates | | | |
| | | CCC | |
| | | cULus | |
| | | EAC | |
| | | RINA | |
| ETIM classification | | | |
| ETIM 8.0 | EC000221 - Front element for push button | | |