

Product designation	Mushroom head pushbutton, Latch, turn key to release Ø 40mm/1.6"		
Product type designation	LPCB684		
<b>General characteristics</b>			
Colour	Black		
Material	Polyamide		
IEC degree of protection	IP66, IP67 and IP69K		
<b>Mechanical features</b>			
Operating force	kg-lb	<0.5Kg / 1.1lb	
Mechanical life - spring return actuators	cycles	500000	
Mechanical life - Latch actuators	cycles	300000	
Mounting adapter	LPXAU120		
Weight	g	83	
<b>UL technical data</b>			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
<b>Ambient conditions</b>			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85
<b>Dimensions</b>			
<b>Certifications and compliance</b>			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates	CCC		
	cULus		
	EAC		
	RINA		
	UL		
<b>ETIM classification</b>			
ETIM 8.0	EC001038 - Front element for mushroom push-button		