

Product designation	Double-touch actuators, spring return white indicator - One extended and one flush pushbuttons		
Product type designation	LPCBL72		
General characteristics			
Colour	Black/Red		
Type of positions	I - O		
Material	Polyamide		
IEC degree of protection	IP66, IP67 and IP69K		
Mechanical features			
Operating force	kg-lb	<0.5Kg / 1.1lb	
Mounting adapter	LPXAU120		
Weight	g	30	
UL technical data			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85
Dimensions			
Certifications and compliance			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates	CCC		
	cULus		
	EAC		
	RINA		
ETIM classification			
ETIM 8.0	EC000221 - Front element for push button		