

Product designation	Push-push button actuators		
Product type designation	LPCQ20		
General characteristics			
Colour	Blue		
Type of positions	Extended. Push on-push off		
Material	Polyamide		
IEC degree of protection	IP66, IP67 and IP69K		
Mechanical features			
Operating force	kg-lb	<0.5Kg / 1.1lb	
Mechanical life - Push-Push actuators	cycles	500000	
Fixing	Without mounting adapter		
Mounting adapter	LPXC10A (1EM) / LPXC01 (1NC)		
Weight	g	27	
UL technical data			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions			
Temperature			
Operating temperature		min	°C -25
		max	°C +70
Storage temperature		min	°C -40
		max	°C +85
Dimensions			
Certifications and compliance			
Compliance			
		CSA C22.2 n° 14	
		IEC/EN/BS 60947-1	
		IEC/EN/BS 60947-5-1	
		UL508	
Certificates			
		CCC	
		cULus	
		EAC	
		RINA	
ETIM classification			
ETIM 8.0	EC000221 - Front element for push button		