

Product designation	Mechanical reset buttons, complete unit, spring return LPCR20		
Product type designation	LPCR20		
General characteristics			
Colour	Red		
Type of positions	Extended. Adjustable length 0...150mm/5.9in		
Material	Polyamide		
IEC degree of protection	IP66, IP67 and IP69K		
Mechanical features			
Operating force	kg-lb	<0.5Kg / 1.1lb	
Mechanical life	cycles	5000000	
Fixing	Without mounting adapter		
Mounting adapter	LPXAU120		
Weight	g	40	
UL technical data			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions			
Temperature			
Operating temperature		min	°C -25
		max	°C +70
Storage temperature		min	°C -40
		max	°C +85
Dimensions			
Certifications and compliance			
Compliance			
		CSA C22.2 n° 14	
		IEC/EN/BS 60947-1	
		IEC/EN/BS 60947-5-1	
		UL508	
Certificates			
		CCC	
		cULus	
		EAC	
		RINA	
ETIM classification			
ETIM 8.0	EC000221 - Front element for push button		