

|                                      |                                              |         |     |
|--------------------------------------|----------------------------------------------|---------|-----|
| Product designation                  | Selector switch actuator key - 3 position    |         |     |
| Product type designation             | LPCS33                                       |         |     |
| <b>General characteristics</b>       |                                              |         |     |
| Type of positions                    | 1 - 0 - 2, key extraction in 2               |         |     |
| Material                             | Polyamide                                    |         |     |
| IEC degree of protection             | IP66, IP67 and IP69K                         |         |     |
| <b>Mechanical features</b>           |                                              |         |     |
| Mechanical life                      | cycles                                       | 1000000 |     |
| Mounting adapter                     | LPXAU120                                     |         |     |
| Weight                               | g                                            | 60      |     |
| <b>UL technical data</b>             |                                              |         |     |
| UL degree of protection              | Type1, 2, 3R, 4, 4X, 12, 12K                 |         |     |
| <b>Ambient conditions</b>            |                                              |         |     |
| Temperature                          | Operating temperature                        |         |     |
|                                      | min                                          | °C      | -25 |
|                                      | max                                          | °C      | +70 |
|                                      | Storage temperature                          |         |     |
|                                      | min                                          | °C      | -40 |
|                                      | max                                          | °C      | +85 |
| <b>Dimensions</b>                    |                                              |         |     |
| <b>Certifications and compliance</b> |                                              |         |     |
| Compliance                           | CSA C22.2 n° 14                              |         |     |
|                                      | IEC/EN/BS 60947-1                            |         |     |
|                                      | IEC/EN/BS 60947-5-1                          |         |     |
|                                      | UL508                                        |         |     |
| Certificates                         | CCC                                          |         |     |
|                                      | cULus                                        |         |     |
| <b>ETIM classification</b>           |                                              |         |     |
| ETIM 8.0                             | EC000222 - Front element for selector switch |         |     |