

Product designation	Selector switch actuator key - 3 position		
Product type designation	LPCS39		
<b>General characteristics</b>			
Type of positions	1 - 0 - 2, key extraction in 1		
Material	Polyamide		
IEC degree of protection	IP66, IP67 and IP69K		
<b>Mechanical features</b>			
Mechanical life	cycles	1000000	
Mounting adapter	LPXAU120		
Weight	g	60	
<b>UL technical data</b>			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
<b>Ambient conditions</b>			
Temperature			
Operating temperature		min	°C -25
		max	°C +70
Storage temperature		min	°C -40
		max	°C +85
<b>Dimensions</b>			
<b>Certifications and compliance</b>			
Compliance			
		CSA C22.2 n° 14	
		IEC/EN/BS 60947-1	
		IEC/EN/BS 60947-5-1	
		UL508	
Certificates			
		CCC	
		cULus	
<b>ETIM classification</b>			
ETIM 8.0	EC000222 - Front element for selector switch		