

Product designation	Selector switch actuator knob - 3 position		
Product type designation	LPCS43		
General characteristics			
Type of positions	1 > 0 - 2		
Material	Polyamide		
IEC degree of protection	IP66, IP67 and IP69K		
Mechanical features			
Mechanical life	cycles	1000000	
Mounting adapter	LPXAU120		
Weight	g	37	
UL technical data			
UL degree of protection	Type1, 2, 3R, 4, 4X, 12, 12K		
Ambient conditions			
Temperature			
Operating temperature			
	min	°C	-25
	max	°C	+70
Storage temperature			
	min	°C	-40
	max	°C	+85
Dimensions			
Certifications and compliance			
Compliance			
	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates			
	CCC		
	cULus		
ETIM classification			
ETIM 8.0	EC000222 - Front element for selector switch		