

Product designation	Monoblock buzzer		
	- Continuous or pulse tone		
Product type designation	LPCZS		
General characteristics			
Material	Polyamide		
IEC degree of protection	IP40 on front and IP20 on rear		
Electrical characteristics			
Rated impulse withstand voltage Uimp	kV	4	
Rated frequency	Hz	50-60	
Supply voltage (AC)	V	9...15	
Supply voltage (DC)	V	9...15	
Mechanical features			
Tightening torque for terminals max	Nm	0.5	
Screwdriver	Flat-head: 0.6x3.5mm/0.02x0.		
Conductor section	AWG/kcmil conductor section		
	min	24	
	max	14	
	IEC		
	min	mm ²	0.5
	max	mm ²	2.5
Weight	g		20
UL technical data			
UL degree of protection	1, 2, 3R, 4, 4X, 12, 12K on front		
Ambient conditions			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates	CCC		
	cULus		
	EAC		
ETIM classification			
ETIM 8.0	EC000130 - Signal horn		