

Product designation	Monoblock buzzer - Continuous or pulse tone LPCZS		
Product type designation	LPCZS		
<b>General characteristics</b>			
Material	Polyamide		
IEC degree of protection	IP40 on front and IP20 on rear		
<b>Electrical characteristics</b>			
Rated impulse withstand voltage Uimp	kV	4	
Rated frequency	Hz	50-60	
Supply voltage (AC)	V	85...140	
Supply voltage (DC)	V	85...140	
<b>Mechanical features</b>			
Tightening torque for terminals max	Nm	0.5	
Screwdriver	Flat-head: 0.6x3.5mm/0.02x0.		
Conductor section	AWG/kcmil conductor section		
	min	24	
	max	14	
	IEC		
	min	mm <sup>2</sup>	0.5
	max	mm <sup>2</sup>	2.5
Weight	g		20
<b>UL technical data</b>			
UL degree of protection	1, 2, 3R, 4, 4X, 12, 12K on front		
<b>Ambient conditions</b>			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85
<b>Dimensions</b>			
<b>Wiring diagrams</b>			
<b>Certifications and compliance</b>			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates	CCC		
	cULus		
	EAC		
<b>ETIM classification</b>			
ETIM 8.0	EC000130 - Signal horn		