

Product designation				LED elements
Product type designation				steady light
Product type designation				LPXLE
<b>General characteristics</b>				
Colour				Green
<b>Electrical characteristics</b>				
Supply voltage (AC)	V			12...30
Supply voltage (DC)	V			12...30
<b>Operations</b>				
Electrical life	hours			100000
<b>Mechanical features</b>				
Tightening torque for terminals max	Nm			1
Conductor section				
	AWG/kcmil conductor section			
		max	12	
	IEC	max	mm <sup>2</sup>	1 or 2 / 2.5
Mounting adapter				LPXAU120
Weight				g 16
<b>Ambient conditions</b>				
Temperature				
	Operating temperature	min	°C	-25
		max	°C	+60
	Storage temperature	min	°C	-40
		max	°C	+85
<b>Dimensions</b>				
<b>Wiring diagrams</b>				
<b>Certifications and compliance</b>				
Compliance	CSA C22.2 n° 14			
	IEC/EN/BS 60947-1			
	IEC/EN/BS 60947-5-1			
	UL508			
Certificates	CCC			
	cULus			
	EAC			
	RINA			
	UL			
<b>ETIM classification</b>				
ETIM 8.0				EC000204 - Lamp holder block for control circuit devices