

Product designation	LED elements steady light base mount on LPZ control station LPXLPB		
Product type designation	LPXLPB		
<b>General characteristics</b>			
Colour	White		
<b>Electrical characteristics</b>			
Rated frequency	Hz	50-60	
Supply voltage (AC)	V	85...140	
<b>Operations</b>			
Electrical life	hours	100000	
<b>Mechanical features</b>			
Conductor section	AWG/kcmil conductor section		
	max	14	
	IEC		
	max	mm <sup>2</sup>	1 or 2 / 2.5
Mounting adapter	LPXAU120		
Weight	g	16	
<b>Ambient conditions</b>			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85
<b>Dimensions</b>			
<b>Wiring diagrams</b>			
<b>Certifications and compliance</b>			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates	CCC		
	cULus		
	EAC		
	RINA		
	UL		
<b>ETIM classification</b>			
ETIM 8.0	EC000204 - Lamp holder block for control circuit devices		