

Product designation	LED elements steady light base mount on LPZ control station		
Product type designation	LPXLPB		
General characteristics			
Colour	Blue		
Electrical characteristics			
Rated frequency	Hz	50-60	
Supply voltage (AC)	V	185...265	
Operations			
Electrical life	hours	100000	
Mechanical features			
Conductor section	AWG/kcmil conductor section		
	max	14	
	IEC		
	max	mm ²	1 or 2 / 2.5
Mounting adapter	LPXAU120		
Weight	g	16	
Ambient conditions			
Temperature	Operating temperature		
	min	°C	-25
	max	°C	+70
	Storage temperature		
	min	°C	-40
	max	°C	+85
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance	CSA C22.2 n° 14		
	IEC/EN/BS 60947-1		
	IEC/EN/BS 60947-5-1		
	UL508		
Certificates	CCC		
	cULus		
	EAC		
	RINA		
	UL		
ETIM classification			
ETIM 8.0	EC000204 - Lamp holder block for control circuit devices		