

Product designation				LED elements
Product type designation				steady light
General characteristics				
Colour				Blue
Electrical characteristics				
Supply voltage (AC)	V			185...265
Supply voltage (DC)	V			185...265
Operations				
Electrical life	hours			100000
Mechanical features				
Tightening torque for terminals max	Nm			1
Conductor section	AWG/kcmil conductor section			
		max	12	
	IEC			
		max	mm ²	1 or 2 / 2.5
Mounting adapter				LPXAU120
Weight		g	16	
Ambient conditions				
Temperature	Operating temperature			
		min	°C	-25
		max	°C	+70
	Storage temperature			
		min	°C	-40
		max	°C	+85
Dimensions				
Wiring diagrams				
Certifications and compliance				
Compliance	CSA C22.2 n° 14			
	IEC/EN/BS 60947-1			
	IEC/EN/BS 60947-5-1			
	UL508			
Certificates	CCC			
	cULus			
	EAC			
	RINA			
	UL			
ETIM classification				
ETIM 8.0				EC000204 - Lamp holder block for control circuit devices