

Product designation	Enclosures
Product type designation	LPZM
General characteristics	
Colour	Grey
IEC degree of protection	IP66 and IP67
Mechanical features	
Weight	g 680
UL technical data	
UL degree of protection	NEMA 4X
Ambient conditions	
Temperature	
Operating temperature	min °C -25 max °C +70
Storage temperature	min °C -40 max °C +85
Dimensions	
Certifications and compliance	
Compliance	IEC/EN 60947-5-1
Certificates	cULus EAC
ETIM classification	
ETIM 8.0	EC000200 - Enclosure for control circuit devices