

Product designation	EMPTY ENCLOSURES		
Product type designation	M2N		
<b>Electrical features</b>			
Maximum operating current ( $\leq 440V$ )	A	32	
<b>Components</b>			
Contactor standard supplied	BF25A, BF26A, BF32A		
Thermal relay to purchase separately	RF38		
<b>Mechanical features</b>			
Weight	g	640	
<b>Ambient conditions</b>			
Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70
<b>Resistance &amp; Protection</b>			
Frontal IP degree	IP65		
<b>Dimensions</b>			
<b>Certifications and compliance</b>			
Compliance	CSA C22.2 n° 14		
	IEC/EN 60947-1		
	IEC/EN 60947-4-1		
	UL508		
Certificates	cULus		
<b>ETIM classification</b>			
ETIM 8.0	EC000200 - Enclosure for control circuit devices		