





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

1	2	3	4	5	6	7	8
REV.	ECN NO.	DATE	SIGN	DESCRIPTION			



Conn.



Pin Assignments
Front View

12	Light Green	淺綠
11	Purple	紫
10	Orange	橙
9	Black	黑
8	Red	紅
7	Pink	粉紅
6	Gray	灰
5	Yellow	黃
4	Green	綠
3	White	白
2	Blue	藍
1	Brown	棕
Conn.	Wire Color Pin Out	

ICD-12AFFM-LL7AXX

XX : 01~99Meters
01 : 01Meter
02 : 02Meters
:
:
99 : 99Meters

Cable Length(L): 01~99Meters

- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP67
 - * Housing: Nylon+GF, Black.
 - * Female Pin: Copper Alloy, Gold Plated.
 - * Lock Nut: Nylon+GF, Black.
 - * O-Ring: Silicon, Gray
 - * Cable: UL2464 24AWG*12C+Drain+Al/My PVC Jacket UV Resistant, OD=7.0, Black.
 - * Cable Length Tolerance: 01M:40mm
02M~05M:±60mm
06M~10M:±100mm
11M~30M:±200mm
31M~99M:±500mm

A	UNIT:mm		TOLERANCE		TITLE			ITEM NO		DRAWN BY		DATE
			±0.5		MIDDLE CNC PIN			DWG NO		Jiazhen_Li		2014-01-10
					CABLE LOCK 12P F CONN F PIN			ICD-12AFFM-LL7AXX		Ruru		2014-01-10
					SCALE	1:1	SIZE	A4	SHEET	1	OF	1
		REV.	A	WC-REV.	A.2	$\varnothing$ Inspection item		CUSTOMER		APPROVED BY		DATE
								ALTW		Jerry		2014-01-10
												8 FMW10702-01-02A1

Amphenol LTW
安費諾亮泰企業股份有限公司