


	1	2	3	4	5	6	7	8			
F					REV.	ECN NO.	DATE	SIGN	DESCRIPTION		
					B	C210625	2021/04/21	Vicky	X8		
					C	C221870	2022/12/01	Vicky	XI		
E											
D											
C					Note: * RoHS Compliant * Important dimension * Waterproof rate: IP67, mated * Connector - Housing: Thermoplastic, Black - Pin: Copper alloy, Gold plated - O-Ring: Rubber, Green - Nut: Thermoplastic, Black - Outer mold: Thermoplastic, Black * Cable: UL2464, PVC Jacket, Black * Cable length tolerance: 1M: +50/-0 mm 1M < L ≤ 3M: +100/-0 mm 3M < L ≤ 5M: +150/-0 mm 5M < L ≤ 10M: ±100 mm 10M < L ≤ 20M: ±200 mm 20M < L ≤ 30M: ±300 mm 30M < L ≤ 99M: ±500 mm						
B											
A	UNIT:mm			TITLE O SEN, M8 W/KEY-PLASTIC CABLE W/SR, F, F, MOLDING				ITEM NO		DRAWN BY	DATE
	TOLERANCE	±0.5mm						DWG. NO 8AP-XXAFFM-SL7AXX		CHECKED BY	DATE
	SCALE 2:1	SIZE A4	SHEET 1 OF 2	CUSTOMER ALTW		APPROVED BY	DATE				
	REV. C	WC-REV. A.4	:Inspection item	安費諾亮泰企業股份有限公司		Jerry	2014-01-09				
	1	2	3	4	5	6	7	8			

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

										6P		5.0	24	8AP-06AFFM-SL7AXX		
										5P				8AP-05AFFM-SL7AXX		
										4P			22	8AP-04AFFM-SL7AXX		
										3P				8AP-03AFFM-SL7AXX		
										2P		4.2	8AP-02AFFM-SL7AXX			
										Contacts		Cable OD	AWG	Item No.		