


F																
E																
D																
C																
B																
A																


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1590198~200	2015/08/27	Mafei	Adding Key Point.
C	C230237	2023/02/23	Vicky	△C X5



△ Note:

- * RoHS Compliant
- * ⌀ Important dimension
- * Waterproof rate: IP67, mated
- * Connector
- Housing: Thermoplastic, Black
- Pin: Copper alloy, Gold plated
- O-Ring: Rubber, Gray
- Gasket: Rubber, Gray
- Outer mold: Thermoplastic, Black
- * Cable: UL2464, PVC Jacket, Black
- * Cable length tolerance: LM: +50/-0 mm

1M < L ≤ 3M: +100/-0 mm
3M < L ≤ 5M: +150/-0 mm
5M < L ≤ 10M: ±100 mm
10M < L ≤ 20M: ±200 mm
20M < L ≤ 30M: ±300 mm
30M < L ≤ 99M: ±500 mm

UNIT:mm		TITLE		Amphenol LTW		ITEM NO	DRAWN BY	DATE
TOLERANCE	±0.5	RBL, D-20A, CABLE W/SR M, F, MOLDING, RBL		安費諾亮泰企業股份有限公司		DWG NO	CHECKED BY	DATE
SCALE	3:4	SIZE	A4	SHEET	1 of 2	DC-XXAMFM-RL7AXX	Joyy	2015/08/27
REV.	C	WC-REV.	A.3	⌀: Inspection item		CUSTOMER	APPROVED BY	DATE
						ALTW	Jerry	2015/08/27

10814-03-B01A2

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

```
-XX:01~99Meters
01:01Meters
02:02Meters
:
99:99Meters
```

△B

UNIT: mm			TITLE RBL, D-20A, CABLE W/SR M, F, MOLDING, RBL 		
TOLERANCE			SCALE 3:4	SIZE A4	SHEET 2 OF 2
± 0.5			REV. C	WC-REV. A.3	QC: Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Mafei	2015/08/27
DWG NO	CHECKED BY	DATE
DC-XXAMFM-RL7AXX	Joyy	2015/08/27
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2015/08/27