



Product Line

Circular Connectors

Power Connectors

M Series Sensor Connectors

USB Connectors

IEEE 1394 Connectors

D-SUB Connectors

DVI Connectors

RJ Connectors

SSL Solution Connectors

LED Indicator

HDMI Connectors

Fiber Optic Connectors

NMEA 2000 Connectors

Cable Joiner

FICX Connectors

Cable Gland - Anti-UV

Vent

> Screw

> Snap-in

> Nut

RBL Connectors

X-Lok Connectors

HS-Lok Connectors

CNC Products

Product Applications

Product Search

Home > Product Line > Vent > Snap-in

☆ Bookmark

Share

Print



Part Number : VENT-BJ003

Connector Body : M-PPE,UL Recognized

Temperature Range : -40°C~105°C

Share 0

Tweet

Share

Download:

2D PDF

Sample 3D model(.igs)

Add to inquiry list

Check inquiry list

Submit inquiry

Description	Details
Connector	Membrane Vent
Field installable	Receptacle
Waterproof Rating	IP68,IP69K
More To Know	Air Permeability: >260ml/min @70mbar, IP68:1M / 60 mins, IP69K:Water with high pressure/steam jet c

* Design and specifications are subject to change without notice.

update: 2014-09-09 00:00:00

