



**Mallory Sonalert Products, Inc.**

Part #: **VSB110-1**

**Sales Outline Drawing**

Revision: **F**

**Specifications:**

Sound Level Category

Mode of Operation

Voltage Rating

Frequency

Loudness @ 2 FT

Current Draw

Housing Material

Storage Temperature

Operating Temperature

Panel Mounting

Knurled Nut

Weight (Typical)

NEMA 3R,4X, & 12

Options

Sound Level Category	Medium
Mode of Operation	Cuckoo (Repeating @ once per second)
Voltage Rating	110/120 VAC
Frequency	2000 Hz
Loudness @ 2 FT	80 dB(A) Typ.
Current Draw	250mA MAX
Housing Material	6/6 Nylon, Color: Black
Storage Temperature	-40° to +85° C
Operating Temperature	-40° to +85° C
Panel Mounting	Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole.
Knurled Nut	Used to attach part to panel. The max recommended torque is 10 in-lbs.
Weight (Typical)	6.2 oz (175g)
NEMA 3R,4X, & 12	Approved with use of ACC03.
Options	Please contact factory.

**Dimensions:** Inches (mm)

