

**Sales Outline Drawing**

**May not be suitable for all medical and aerospace applications.  
Specifications: Contact Mallory Sonalert to discuss your application.**

**NO CIRCUITRY**

Oscillation Frequency (Hz)	2700 ± 300
Operating Voltage (Vdc)	2.0 ~ 5.0
Rated Voltage (Vdc)	3.3
Current Consumption Max. (mA)	30 at Rated Voltage
Sound Pressure Level (dB min)	85 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-40 ~ +85
Storage Temperature (°C)	-40 ~ +85
Lead Pin	Tin Plated Brass
Housing	PPO plastic resin (Color: Black)
Weight (Grams)	0.8
Condition by wave soldering (°C)	260 ±5 / within 5 sec
Condition by hand soldering (°C)	350 ±20 / within 5 sec
Options	For other options contact factory

**Dimensions:** (units: mm)**RoHS Compliant**