

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

Resonant Frequency (Hz)	4100 ± 500
Operating Voltage (Vdc)	3 ~ 15
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	12 at Rated Voltage
Sound Pressure Level Min. (dB)	83 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
LED Color	GREEN
Operating Temperature (°C)	-20 ~ +100
Storage Temperature (°C)	-30 ~ +110
Housing	PBT (Color: Hyaline)
Leading Pins	Tin Plated Brass
Weight (Grams)	1.0
Condition by Wave (°C)	260 ± 5 within 5 seconds
Condition by Hand (°C)	350 ± 20 within 5 seconds
Options	For other options contact factory

Dimensions: (units: mm)

ROHS Compliant

