



**Mallory Sonalert Products, Inc.**

Part #:

**ZA028SDDL1**

**Sales Outline Drawing**

Revision:

**B**

**Specifications:**

|                       |   |
|-----------------------|---|
| Sound Level Category  | Soft  |
| Mode of Operation     | 10 Sec On-Delay Continuous  |
| Voltage Rating        | 16 to 28 VDC  |
| Frequency             | 3300 ± 500 Hz   |
| Loudness @ 2 FT       | 65 to 75 dB(A) Typ.   |
| Current Draw          | 40mA MAX  |
| Housing Material      | 6/6 Nylon, Color: Black   |
| Storage Temperature   | -40° to +80° C  |
| Operating Temperature | -30° to +65° C  |
| Panel Mounting        | Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole. |
| Knurled Nut           | Used to attach part to panel. The max recommended torque is 10 in-lbs.        |
| Weight (Typical)      | 28 g  |
| NEMA 3R, 4X, & 12     | Approved with use of included gasket.   |
| Options               | Please contact factory.   |

**Dimensions:** Inches (mm)

**cUL Recognized**

**ROHS Compliant**

