

	UNITS	
NUMBER OF TERMINALS		11
ELECTRICAL RATING		
Nominal Voltage Rating:	Volts	300
Nominal Current Rating:	Amps	15
DIELECTRIC STRENGTH		
Output to Adjacent output Terminals:	V rms	2000
Output to Input Terminals:	V rms	2000
Terminals to Rail Chassis:	V rms	2000
CONSTRUCTION		
Protection Category (Finger Safe):	IEC	N / A
Internal Metal Tracks:		Copper Alloy, Zinc Plated
Screws Terminals:		Steel, Zinc Plated
Screw Style and Size:	mm	Combination Head, M3.5 x 0.06 x 5.08
Screw Terminal Torque Maximum:	Lb-in / Nm	9 / 1.01
TEMPERATURE		
Operating, Lower:	°C	-40
Operating, Upper:	°C	+80
MISCELLANEOUS		
Chassis Mount Screw Torque:	Lb-in / Nm	8 - 10 / 0.90 - 1.13
Flammability Rating:		94V-0
Wire Size:	AWG/mm2	20-12 / 0.5 - 3.0
Body Color:		Light gray
DIN Locking Clip Color:		Red
Weight:	grams	51



HOI
ORI

S'


↑

70


904

7...26

PHONE: (843) 393-5778 FAX: (843) 393-4123 EMAIL: info@magnecraft.com



.D DOWN CLIPS ARE
ORDERED SEPARATELY



ALTERNATE NEMA
OR IEC () NUMBERS
VIEWED FROM
PIN SIDE

Mating Relays

788, A283

See section 1

388TDR, TDRSOXB

See section 4

Mating Hold Down Clips

(788) **16-1352**

(A283) **16-1340**

(388TDR) **16-1239 Long Body**

(TDRSOXB) **16-1239**

STANDARD PART NUMBER	DESCRIPTION
- 463 - 1	11 PIN SOCKET, DIN/PANEL MOUNT, WITH SCREW TERMINALS & CLAMPING PLATES.