

SPECIFICATION:

Electrical





Current Rating: 4A Max.
 Insulation Resistance: 100 MΩ Min. @ 500V DC
 Operating Temp.: -20°C to +85°C
 Degree of Protection: IP 67
 Mating Cycles: 100 Insertions

Material


Insulator: Thermal Plastic UL94V-0
 Contacts: Copper Alloy
 Shell: Steel

Contact Plating


Underplate: 50μ" ~ 150μ" Nickel
 Contact Area: 1μ" ~ 15μ" Gold
 Solder Tails Area: 100μ" Tin Min.



(8 pins)



(5 pins)



(4 pins)

Part Number	Number of Pins
25-814-0	4
25-815-0	5
25-818-0	8

TITLE		SCALE
WATERPROOF (IP67) INLINE JACK		NTS
DRAWING NO. 25-81X		
		UNITS mm
FILE NAME	25-81X.pdf	SHEET 1/1



Mode Electronics Part Number 'multi-parts'