



**SPECIFICATIONS:**

**Electrical**

Rating: 100VAC @ 1A  
 Insulation Resistance: Over 100 Megaohms @ 500VDC  
 Dielectric Strength: 250VDC for 1 Minute

**Materials**

A. Cover: EVA  
 B. Metal Part: Steel Nickel Plated  
 C. Insulator: PBT  
 D. Pin Contact: Brass Nickel Plated

Part Number	Number of Pins
25-230-0	3
25-240-0	4
25-250-0	5
25-260-0	6
25-280-0	8

TITLE		SCALE
INLINE DIN PLUGS		NTS
DRAWING NO.	25-2X0	
		UNITS mm
FILE NAME	25-2X0.pdf	SHEET 1/1



Mode Electronics Part Number 'multi-parts'