



SPECIFICATIONS:

Materials

Insulator: 30% Glass fiber PBT
(D type: NYLON 65)
Flame Classification: UL94V-0
Contact Material: Phosphor Bronze
Contact Plating: 50 μ ” Nickel (Underplate)
Gold Flash (Contact Area)
Insulator Color: Black (**36-101-0**)
Red (**36-102-0**)

Electrical

Current Rating: 3 Amps
Contact Resistance: 20 m Ω Max. at DC 100mA
Insulation Resistance: 5000 M Ω Min. at 500 VDC
Dielectric Withstanding: 500 VAC for one minute
Operating Temp.: -55 $^{\circ}$ C to 105 $^{\circ}$ C

TITLE		SCALE
LONG HANDLE SHUNT		NTS
DRAWING NO.	36-101/102	
		UNITS mm
FILE NAME	36-101&102.pdf	SHEET 1/1



Mode Electronics Part Number 'multi-parts'