



Pin Hole Layout  
(Jack Bottom View)



5	Housing	1	PBT	Black Color
4	Barrel	1	Brass	Nickel Plated
3	Tip Spring	1	0.25T TicuR1-M-EH	Silver Plated
2	Ring Spring	1	0.2T TicuR1-M-EH	Silver Plated
1	Earth Terminal	1	0.2T Phosphor Bronze	Silver Plated
Item #	Item Name	QTY	Material	Finish

**Specifications:**

Contact resistance: 30mΩ Max.  
 Insulation resistance: 100MΩ Min @ DC 500V  
 Dielectric Withstanding Voltage: AC 500V for one minute

TITLE		SCALE
<b>STEREO PC MOUNT JACK</b>		<b>NTS</b>
DRAWING NO. <b>24-392</b>		
		UNITS <b>mm</b>
FILE NAME <b>24-392.pdf</b>		SHEET <b>1/1</b>