



NOTE:

Electrical

Overall Resistance: 10KΩ ± 20%
 Rated Power: 0.1W
 Rated Voltage: 150V AC
 Residual Resistance: Terminal 1-2: < 3Ω; Terminal 2-3: < 5Ω
 Rotational Noise: Less than 47mV
 Insulation Resistance: 500V DC, >100MΩ
 Withstand Voltage: 1 minute at 800V AC

Mechanical

Total Rotation Angle: 300° ± 5°
 Rotational Life: 10,000 cycles
 Operating Temperature: -20°C - 50°C

TITLE		SCALE
PC MOUNT ROTARY POTENTIOMETER		2 : 1
DRAWING NO. 62-284		
		UNITS mm
FILE NAME	62-284.pdf	SHEET 1/1



Mode Electronics Part Number 62-284-0