



**SPECIFICATIONS:**

**Electrical**

Rated Power: 0.1W  
 Rated Voltage: 150V AC  
 Residual Resistance: Terminal 1-2: < 5Ω; Terminal 2-3: <10Ω  
 Rotational Noise: Less than 47mv  
 Insulation Resistance: 500V DC, >100MΩ  
 Withstand Voltage: 1 minute at 500V AC  
 Switch Contact Resistance: Less than 1Ω

**Mechanical**

Total Rotation Angle: 260° ± 5°  
 Switch Action Angle: 30° ± 10°  
 Switch Circuit: S.P.S.T.  
 Rotational Life: 10,000 cycles  
 Operating Temperature: -20°C - 50°C

Mode Part #	Overall Resistance	Type
62-222-0	1KΩ ± 20%	Linear
62-223-0	5KΩ ± 20%	Linear
62-224-0	10KΩ ± 20%	Linear
62-254-0	10KΩ ± 20%	Log
62-227-0	100KΩ ± 20%	Linear
62-229-0	1MΩ ± 20%	Linear

TITLE		SCALE
ROTARY POT. WITH 1AMP SWITCH		2 : 1
DRAWING NO. 62-2XX(1)		
		UNITS mm
FILE NAME	62-2XX(1).pdf	SHEET 1/1



**Mode Electronics Part Number 'multi-parts'**