


**MARKING**  
 production code EN60062/factory code  
*Produktionscode EN60062/Fertigungsstätte*

**NUT**  
 nut M10x1 DIN439, type B  
 low form, brass  
*Mutter M10x1 DIN439, Typ B  
 niedrige Form, Messing*

**MAGNET**  
 AlNiCo 500 (p/n 4003004003)  
 magnetized axial  
*AlNiCo 500 (Art.-Nr. 4003004003)  
 axial magnetisiert*



tolerances according to DIN ISO 2768 m

Special Product Data	Conditions	Min	Typ	Max	Unit
Sealing compound		Voltatex CE 12 FW-UL			
Housing material		brass			

Mag. values DIN IEC 60404-8-	Conditions	Min	Typ	Max	Unit
Energy product (B x H) max.		35	39,8		kJ/cu m
Remanence Br		1.120	1.240		mT
Revers. temp. coeff. of Br			-0,02		%/K
Max. operating temperature				450	°C
Magnetic moment	measured with MS150	19,8	22,2		E-6 Vs*cm