



# 1/2" JAC Junction Blocks

4, 6 & 8 Port, 3 Pin JAC Junction blocks



Straight Wiring | MIN Receptacles | 24 - 120 Volt | IP67 Rating



Trunk Style	Trunk Connection	# of Ports	JAC Version Part Number	Mating Cable Part Number	Port Connection
	MIN Size I 3 Pole Male Receptacles	4	JAC-430-003-M000	MIN-3FP-*	
		6	JAC-630-003-M000		
		8	JAC-830-003-M000		

### Specifications:

Ratings:	3 A per Connector 8 A per Block
Voltage:	0-150 Volt Max
Body:	Polypropylene
Inserts:	Polyamide
Port Coupling Nuts:	Nickel Plated Brass
O-Ring:	BUNA-N
LED Lens:	Polycarbonate
Contacts:	Copper Alloy with Gold Plating
Marker Tags:	Polyamide (supplied on all units)

JAC Junction Blocks

R