



MCV (M23) Series Cordsets

19 Conductor M23 Series Cordsets, 18/22AWG



Straight Female Cordsets | 150V, 10 & 1A | 150V, 9 & 2A | IP69 Rating



18 AWG					
Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MCV-19FPX-**-C010	Black PVC ITC-ER/PLTC-ER 19 X 18 AWG 150V 10/1A or 9/2A -40°C to +90°C 13.6mm OD	PVC ITC-ER/PLTC-ER	1. Violet 2. Red 3. Gray 4. Red/Blue 5. Green 6. Blue 7. Gray/Pink 8. White/Green 9. White/Yellow 10. White/Gray 11. Black 12. Green/Yellow 13. Yellow/Brown 14. Brown/Green 15. White 16. Yellow 17. Pink 18. Gray/Brown 19. Brown	 M23 x 1
18/22 AWG					
	MCVP-19FP-**	Black PUR AWM With Foil Shield 3 X 18 AWG 150V, 10A or 9A 16 X 22 AWG 150V, 1A or 2A -40°C to +80°C 9.9mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR Foil Shield	1. Violet 2. Red 3. Gray 4. Red/Blue 5. Green 6. Blue*** 7. Gray/Pink 8. White/Green 9. White/Yellow 10. White/Gray 11. Black 12. Green/Yellow*** 13. Yellow/Brown 14. Brown/Green 15. White 16. Yellow 17. Pink 18. Gray/Brown 19. Brown***	 M23 x 1
	MCVWF-19FP-**	Black TPE AWM 3 X 18 AWG 150V, 10A or 9A 16 X 22 AWG 150V, 1A or 2A -40°C to +80°C 9.4mm OD	Continuous-Flex (10 MM Cycle) Weld Slag Resistant TPE		

E
M23 Series

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

*** Brown, Blue and Green/Yellow are 18AWG

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MCVP-19FP-1M becomes MCVP-19FP-1M-SS)