



# MDC (M12) Series Cordsets

4 Conductor MDC Series Cordsets, 22AWG



Straight Male Cordsets | 300 Volt, 4 amps | IP69 Rating



H

Micro-DC (M12) Series Cordsets

Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MDC-4MP-** (Yellow)  MDC-4MP-**-B (Black)	PVC AWM <b>4 X 22 AWG</b> 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC	1. Brown 2. White 3. Blue 4. Black	 M12 x 1
	MDCM-4MP-**	Yellow PVC AWM With Foil Shield <b>4 X 22 AWG</b> 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC Foil Shield		
	MDCM-4MSP-**	Yellow PVC AWM With Foil Shield <b>4 X 22 AWG</b> 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC  Foil Shield to the Coupling Nut		
	MDCP-4MP-**	Yellow PUR AWM <b>4 X 22 AWG</b> 300V, 4A -40°C to +80°C 5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		
	MDCW-4MP-**	Yellow TPE AWM <b>4 X 22 AWG</b> 300V, 4A -40°C to +80°C 5mm OD	Weld Slag Resistant TPE		
	MDCWF-4MP-**	Black TPE AWM <b>4 X 22 AWG</b> 300V, 4A -40°C to +80°C 5mm OD	Hi-Flex Weld Slag Resistant TPE		
		MDCPQ-4MP-**	Yellow PUR AWM <b>4 X 22 AWG</b> 300V, 4A -40°C to +80°C 5mm OD		

\*\* Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult factory for other lengths.

Black and gray cables are available on some versions, please consult the factory.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "SS" suffix. (e.g. MDC-4MP-1M becomes MDC-4MP-1M-SS)