



MDC (M12) Series Splitters

3, 4 & 5 Conductor MDC Series Splitters



Splitters | 300 Volt, 4 amps | 60 Volt, 3 amps | IP67 Rating

H

Micro-DC (M12) Series Cordsets

Housing Style	Rating	Part Number	Circuit
	300V 4A	MDC-44YFF	
	300V 4A	MDC-45YFF	
	300V 4A	MDC-55YFF	
	60V 3A	MDNT-43YFF-B	

Specifications:

- Body: Industry Standard PVC
- Insulator: Polyamide
- Contacts: Copper Alloy with Gold Plating
- Coupling Nut: Nickel Plated Brass
- O-Ring: BUNA-A
- Temperature: -40°C to +105°C (-40°F to +221°F)