



MDC (M12) Series Cordsets

2 & 3 Conductor MDC Series Cordsets, 18/20/22AWG



Right Angle Female Cordsets | 300 Volt, 4 amps | IP69 Rating



Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MDC-2FPX-**-R	Yellow PVC AWM 2 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD	Industry Standard PVC	1. Not Used 2. Not Used 3. Brown 4. Blue 5. Not Used	 M12x1
	MDC-2FP-**-R	Yellow PVC AWM 2 X 20 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC		
	MDC-3FPX-**-R	Yellow PVC AWM 3 X 18 AWG 300V, 4A -40°C to +105°C 7.4mm OD	Industry Standard PVC	1. Brown 2. Not Used 3. Blue 4. Black 5. Not Used	 M12x1
	MDC-3FP-**-R	Yellow PVC AWM 3 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC		
	MDCM-3FP-**-R	Yellow PVC AWM With Foil Shield 3 X 22 AWG 300V, 4A -40°C to +105°C 5mm OD	Industry Standard PVC Foil Shield		
	MDCP-3FP-**-R	Yellow PUR AWM 3 X 22 AWG 300V, 4A -40°C to +80°C 5mm OD	Oil and Cutting Fluid Resistant Cut Resistant PUR		

** Lengths in meters. Standard cable lengths are 1, 2, 4, 5, 6, 10 & 15 meters. Consult the factory for other lengths.

2~5 Pole females will have all 5 contact holes in the connector.

Standard coupling nut is nickel plated brass, for stainless steel coupling nut add a "-SS" suffix. (e.g. MDC-3FPX-1M-R becomes MDC-3FPX-1M-R-SS)

H

Micro-DC (M12) Series Cordsets