



# 7/8" MIN Power Series Cordsets

## 3 & 4 Conductor MIN Power Series Size I Cordsets, 14AWG



Straight & Right Angle Cordsets | 600V, 18A | 600V, 15A | IP69 Rating



D

MIN Power Cordsets

Male Straight					
Connector Body Style	Part Number	Cables	Features	Color Code	Faceview
	MINH-3MP-**	Gray PVC STOOW <b>3 X 14 AWG</b> 600V, 18A -40°C to +105°C 13.7mm OD	Industry Standard PVC	<b>North American</b> 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MINH-4MP-**	Gray PVC STOOW <b>4 X 14 AWG</b> 600V, 15A -40°C to +105°C 14.9mm OD	Industry Standard PVC	<b>North American</b> 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2
Female Straight					
	MINH-3FP-**	Gray PVC STOOW <b>3 X 14 AWG</b> 600V, 18A -40°C to +105°C 13.7mm OD	Industry Standard PVC	<b>North American</b> 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MINH-4FP-**	Gray PVC STOOW <b>4 X 14 AWG</b> 600V, 15A -40°C to +105°C 14.9mm OD	Industry Standard PVC	<b>North American</b> 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2
Female Right Angle					
	MINH-3FP-**-R	Gray PVC STOOW <b>3 X 14 AWG</b> 600V, 18A -40°C to +105°C 13.7mm OD	Industry Standard PVC	<b>North American</b> 1. Green/Yellow 2. Black 3. White	 7/8"-16UN2
	MINH-4FP-**-R	Gray PVC STOOW <b>4 X 14 AWG</b> 600V, 15A -40°C to +105°C 14.9mm OD	Industry Standard PVC	<b>North American</b> 1. Black 2. White 3. Red 4. Green/Yellow	 7/8"-16UN2

\*\* Lengths in meters. Standard cable lengths are 1, 2, 5, 10 & 15 meters. Consult the factory for other lengths.

Standard coupling nut is nickel plated brass, for stainless coupling nut add a "-SS" suffix. (e.g. MINH-4FP-3 becomes MINH-4FP-3-SS)

TPE jacket (TC-ER) is available upon request.