



NAN (M8) Series Field Wireable Plugs

3 & 4 Conductor NAN Series Field Wireable Plugs, 22-24AWG



Field Wireable Plugs | Axial Piercing | 60V, 3 amps | IP67 Rating




# of Poles	Male Faceview	Wire AWG Rating	Cable O.D. Range	Male Plugs		Female Plugs	
				Straight	Right Angle	Straight	Right Angle
3	 M8 x 1	18-24 AWG 60V 3A	4-5 mm	NAN-T-3MP-FW	NAN-T-3MP-FW-R	NAN-T-3FP-FW	NAN-T-3FP-FW-R
4	 M8 x 1	18-24 AWG 60V 3A	4-5 mm	NAN-T-4MP-FW	NAN-T-4MP-FW-R	NAN-T-4FP-FW	NAN-T-4FP-FW-R

J
NAN (M8) Series

Specifications:


Body: Oil Resistant Black PVC
 Insulator: Polyamide
 Contacts: Copper Alloy with Gold Plating
 O-Rings: NBR
 Coupling Nut: Nickel Plated ZnAl
 Grommet: NBR
 Connection: Axial Piercing
 Temperature: -25°C to +90°C (-13°F to +194°F)

Straight




Male Plug


Right Angle



Male Plug



Female Plug



Female Plug