


 You're here: [Home](#) / [ILME Rectangular Connectors](#) / [Plastic, T Series, Rectangular Cover, size 77.27, 4 Pegs](#)


Plastic, T Series, Rectangular Cover, size 77.27, 4 Pegs

Part # TCHC-16

Stock: 5 in stock.

 Qty:

[Email this Product](#)
[Add to Product List](#)

Quick Overview

Cover for IP65 Rectangular Connector, Size 77.27

My Cart

You have no items in your shopping cart.

Mencom Newsletter

Join our newsletter & receive the latest news from Mencom


[Chat online now](#)

Chat with us online during business hours, 8 - 5 EST

Specification	Description	Mating Base	Downloads
---------------	-------------	-------------	-----------

Product Type	Rectangular Connectors		
ILME Series	T		
Mencom Series	N/A		
Component Type	Cover		
Housing/Insert Type	T-Type		
Lever Type	N/A		
Pegs	4 Pegs		
Hood Entry	N/A		
Hood Thread	N/A		
Enclosure Dimension	77.27		
Number of Entries	0		
Gasket	No		
Pin Count	N/A		
Insert Dimension	77.27		
Gender	N/A		
Contact Plating	N/A		
Double Insert	N/A		
Voltage Rating	N/A		
Amperage Rating	N/A		
Mounting Style	N/A		
Cover	Yes		
Upper AWG	N/A		
Lower AWG	N/A		
Termination	N/A		
Enclosure Material	Plastic		
Temperature Range in Degrees Celsius	-40 C to +90 C		
IP Rating	IP65		
Weight (lbs.)	0.0850		

