



## 3M Defense

[Products](#) | [Capabilities](#) | [About 3M Defense](#) | [Support](#)

[United States](#) > [All 3M Products](#) > [Market Segments](#) > [Manufacturing and Industry](#) > [3M Defense US](#) > [Defense Products](#) > [Electrical Products](#) > [Electrical Tapes](#) > Scotch® Vinyl Mastic Roll 2210-4x10FT, 4 in x 10 ft 102 mm x 3,05 m), 10 per case

# Scotch® Vinyl Mastic Roll 2210-4x10FT, 4 in x 10 ft 102 mm x 3,05 m), 10 per case

3M ID 80050049008 UPC# 00054007112228 3M Product Number 2210-4X10FT



This 90 mil, 4 in x 10 ft (102 mm x 3,05 m) roll is compatible with solid dielectric cable insulation, is temperature-rated to 176°F (80°C) and has an inner unit pack of 1 roll per box with 10 rolls per case.

### Overview

### Support

This Scotch® Vinyl Mastic Roll 2210 is self-fusing, rubber-based insulating compounds laminated to a flexible, with an all-weather grade PVC backing. Resistant to abrasion, moisture, alkalis, acid, copper corrosion, UV and varying weather conditions. This conformable roll is excellent for insulating, moisture-sealing and pad connections up to 600V.

### Specifications

<b>Adhesive Material</b>	Mastic
<b>Backing Material</b>	Polyvinyl Chloride
<b>Breaking Strength</b>	20 Ib/in
<b>China RoHS - Below MCV</b>	Yes
<b>Color</b>	Black
<b>EU RoHS Compliant</b>	Yes
<b>Length</b>	10 Linear Foot
<b>Product Family</b>	Scotch® Vinyl Mastic Tapes 2200 and 2210
<b>Tape Grade</b>	Premium
<b>Tape Type</b>	Sealing and Insulating Mastic
<b>Thickness</b>	90 Milli-inch (mil)
<b>Voltage Application</b>	Low Voltage
<b>Width</b>	4.0 Inch