



Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshows | Support

[United States](#) > [Products & Services](#) > [Electronics, Electrical, and Communications](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Electrical Wire Connectors and Tools](#) > [Insulation Displacement Connectors and Tools](#) > [3M™ Scotchlok IDC Connectors for Electrical Applications](#) > 3M™ Scotchlok™ Electrical IDC 562-BIN, Double Run or Tap, Flame Retardant, Yellow, 12 AWG (solid/stranded), 10 AWG (stranded), 1000 per case

[Find An Account Rep](#) [Where To Buy \(Find A Distributor\)](#) [Contact Us](#)

3M™ Scotchlok™ Electrical IDC 562-BIN, Double Run or Tap, Flame Retardant, Yellow, 12 AWG (solid/stranded), 10 AWG (stranded), 1000 per case

UPC# 00054007110408 3M Product Number 11040 3M Product Number 562-BIN 3M ID 80601103189

- [Print](#)
- [Share](#)




12 (3,0) AWG Solid/Stranded 10 (4,0) AWG Stranded, Yellow, 1000 per bin

Need Help?

Questions? We can help
[Contact Us](#)

Network Access Message: The page



Overview | Support

Specifications

Agency Approvals	UL
China RoHS - Below MCV	Yes
Color	Yellow
Conductor Sizes	12 AWG / 10 AWG Stranded
Connection Type	Double Run or Tap
Connector Style	Insulation Displacement
EU RoHS Compliant	Yes
Flame Retardant	Yes
Maximum Operating Temperature (Celsius)	90 Degree Celsius
Maximum Operating Temperature (Fahrenheit)	194 Degree Fahrenheit
Maximum Recommended Voltage Rating	600 Volt
Maximum Wire Gauge	10 AWG
Minimum Wire Gauge	10 AWG
Packaging	Bin
Product Family	IDC for Electrical Applications

