

3M™ Scotchlok™ IDC Tap Connector UB2A Box

UPC# 00051115261893 3M Product Number UB2A(BX) 3M ID 80611327471



UB2A/UB2A-D connectors have a pre-crimp feature that gives the craftsperson a time-saving edge. By positioning the connector on the conductor and pre-crimping, the conductor is prevented from slipping out of the connector before the crimp is completed.

Benefits

- Gel filled for Moisture Resistance and for PIC Cable Applications
- 19-26 AWG
- 2.08mm/.082" Maximum Insulation
- O.D.
- Polypropylene
- UL Listed

 **Network Access Message:** The page cannot be displayed

Support

Suggested Applications

- Enabling the user to tap into another wire without interrupting service

A factory installed sealant protects against corrosion and seals out moisture. The UB2A/UB2A-D connectors permit tapping directly onto an existing conductor without interrupting service. In ready access closures, these connectors eliminate cutting cable pairs, opening circuits, and piecing out wires. Choose any one of the 3M[®] Scotchlok[™] Crimping Tools E-9 to use with the UB2A connector.

Specifications

Cable Type	PIC
Composition	Filled
Connector Type	Bridge Tap/2 Conductor
Flame Retardant	No
Insulation Outside Diameter	0.082 Inch
Operating Temperature Range	-40 to 285 Degree Fahrenheit
Product Family	IDC for Communications Applications
Product Type	Splices, Connectors, and Modules
RUS Listed	Yes/BA

People who viewed this item also viewed



3M™ Scotchlok™ IDC Tap Connector UPB Bulk



3M™ Scotchlok™ Electrical
IDC 905N, Double Run or Tap
Self-Stripping, Low Voltage
(Automotive) Applications.



3M™ Scotchlok™ Moisture Guard Connector, 100 per jug



3M™ Scotchlok™ Electrical
IDC 557-BULK, Pigtail, Self-
Stripping, Moisture Resistant
and Flame Retardant. Red.

3M™ Scotchlok™ IDC Butt
Connector UP2 Bulk